


Application examples (Stator/Rotor)

							Stator	
							Rotor	
T30SC	T30CC	T20MC	T30SF	T30CF	T30MF	T30EF	Model	
Standard rotor	Cutter rotor	Mixing rotor	Standard rotor	Cutter rotor	Mixing rotor	Emulsifying rotor	Fuction	
Stainless steel 316L PTFE	Stainless steel 316L PTFE	Stainless steel 316L PTFE	Stainless steel 316L PTFE	Stainless steel 316L PTFE	Stainless steel 316L PTFE	Stainless steel 316L PTFE	Material in Contact with Product	
100~3000ml	100~3000ml	100~3000ml	100~3000ml	100~3000ml	100~3000ml	100~3000ml	Working Range(ml)(H ₂ O)	
Ø30mm	Ø30mm	Ø30mm	Ø30mm	Ø30mm	Ø30mm	Ø30mm	Stator diameter	
Ø23mm	Ø23mm	Ø23mm	Ø23mm	Ø23mm	Ø23mm	Ø23mm	Rotor Diameter	
36m/s	36m/s	36m/s	36m/s	36m/s	36m/s	36m/s	Circumferential Speed	
220mm	220mm	220mm	220mm	220mm	220mm	220mm	Tool Length	
40/175mm	40/175mm	40/175mm	40/175mm	40/175mm	40/175mm	40/175mm	Min/Mix. Immersion Depth	
20-50µm	20-50µm	20-50µm	20-50µm	20-50µm	20-50µm	20-50µm	Suspension	Ultimate fineness
1-10µm	1-10µm	1-10µm	1-10µm	1-10µm	1-10µm	1-10µm	Emulsion	
All methods	All methods	All methods	All methods	All methods	All methods	All methods	Sterilization Methods	

